

# Full-automatic 3-ply Disposable Face Mask Pad Machine

## ■ Features

The equipment mainly processes non-woven fabric feeding, folding and pressing, nose bar positioning, and face mask molding, with full-automatic control and smooth operation that only need material feed regularly without manual work. Its product features smooth respiration, comfort, good filtering effect, and fit for the human face.

Whole set of the equipment is suggested:  
 SMKS-A\*1+SABW\*4+SCI-300W-2000L(option)\*1  
 (adjustable H=700~1000mm).



3-ply face mask tablet machine

## ■ Specifications

Model	SMKS-A
Power	220V/50Hz
Required Air Pressure(mpa)	0.4-0.7
Productivity(pcs/min)	Max.140
Use Environment	Dust-free Workshop


We reserve the right to change specifications without prior notice.



## Semi-automatic Face Mask Ear-loop Machine

### Workflow

- Manually insert the face mask without ear loops into the machine
- Press the start button
- Bond one side of the face mask
- Bond another side of the face mask after rotating it



### Specifications

Model	SABW
Applicable Range	Face Mask Ear-loop Bonding
Face Mask Type	3-Ply Disposable
Required Air Pressure (Mpa)	0.4-0.7
Bolding Method	Ultrasonic
Ultrasonic Power(KW)	2
Power	220V/50Hz
Use Environment	Dust-free Workshop
Dimension(W×D×H)	1400×820×1480

We reserve the right to change specifications without prior notice.

### Shini Group

Addr.: No. 23, Minhe St., Shulin Dist., New Taipei, Taiwan

Tel: +886 2 2680 9119

FAX: +886 2 2680 9229

Email: shini@shini.com