
Accessories

ACF





Features

- ACF filter with SAL-G hopper loader in the dusty application.
- It is mounted on vacuum line of the main vacuum unit.
- It features a detachable dust collection bin and reduces the maintenance cycle.

Model		Capacity (H×W×D)	Pipe diameter (inch)
ACF-1	mm	550×220×235	1.5
ACF-1	inch	21.7×8.7×9.3	
ACF-2	mm	550×220×235	2.0
ACF-2	inch	21.7×8.7×9.3	2.0

MST-S


100, 200, 300 and 500kgs material storage tank for SSC screw feeding application.

Model	MST-	100S	2005	3005	500S
	mm	1287	1387	1637	1726
Н	inch	46.5	50.8	60.6	64.2
W	mm	621	821	943	1243
VV	inch	24.2	32	36.6	48.8
D	mm	625	825	947	1247
	inch	24.2	32	36.6	48.8
Weight	kg	52	66	80	110
vveigne	lb	115	146	176	243



SVH/SMH Series

■ Coding Principle



Features


- This series of hopper receiver can work with most of the main vacuum units, such as SAL-G and SAL-UG series.
- SMH receiver is suitable for mounting on the dryer, storage tank, or machine hopper.
- SVH receiver is designed to be mounted directly on feeding throat of the plastic processing machine. It required no machine hopper and kept very little dried material before the process.
- Stainless steel hopper receiver
- Standard equipped with steel wired mesh filter screen


Accessory & Options


- SMH-6L/12L can work with storage collective hopper SCH-6L in the direct feeding throat mounting application.
- Optional enhanced mixing technology for proportional valve SPV-U application. Add "QM" at the end of the model code.

SVH/SMH Series

Outline Drawings







Base Flange

SVH Specifications

		Conveying pipe dia	Vacuum pipe dia.			
Model	Capacity (L)	Dimension H×W×D (mm)	Weight (kg)	(inch)	(inch)	
SVH-3L	3	460×260×315	3	1.5	1.5	
SVH-6L	6	600×260×305	7	1.5	1.5	
SVH-12L	12	700×300×365	11	1.5	1.5	
SVH-24L	24	1120×360×375	13	2	2	

SVH Base mounting dimensions

Model	L(mm)	L1(mm)	D(mm)	R(mm)
SVH-3L	120	50	40	6.5
SVH-6L	150	70	55	6.5
SVH-12L	180	80	55	6.5
SVH-24L	180	80	80	6.5

SMH Specifications

	Receiver					
	Capacity (L)	Dimension H×W×D (mm)	Weight (kg)	Conveying pipe dia. (inch)	Vacuum pipe dia. (inch)	
SMH-6L	6	460×260×315	7	1.5	1.5	
SMH-12L	12	515×325×350	7	1.5	1.5	
SMH-24L	24	720 × 325× 375	9	2	2	

SMH Base mounting dimensions


	L(mm)	L1(mm)	L2(mm)
SMH-6L			
SMH-12L	210	180	146
SMH-24L			



SHR-U

SHR-U Series

■ Coding Principle




Features

- This series of hopper receiver can work with the most of main vacuum units and Shini compact dryer SCD. SAL-UG series required 6 pins receiver, and SCD series required 4 pins receiver.
- SHR-U receiver is suitable for mounting on the dryer, storage tank, or machine hopper.
- Stainless steel hopper receiver.
- Standard equipped with steel wired mesh filter screen.



Air accumulator




Multifunctional installation frame

■ Accessory & Options

- Multi-functional installation frame HMB suitable for other mounting application with max. 900mm adjustable diameter.
 Add "HMB" at the end of the model code.
- SHR-U can work with storage hopper collective hopper SCH-U/SICH-U in the direct feeding throat mounting application.
- Optional enhanced mixing technology for proportional valve SPV-U application. Add "QM" at the end of the model code.
- In case of conveying highly dusty material, SHR-12U and above can be equipped with air accumulator for auto purging function to reduce the maintenance cycle. Add "A" at the end of the model code.
- Anti-bridge option at the material outlet for SHR-48U. Applicable for flowing material but bridging from time to time only. Add
 "MB" at the end of the model code.

SHR-U-(E) Series

Outline Drawings



■ Specifications


		Receiver		6	Vacuum Pipe Dia.	
Model	Capacity (L)	Dimension(H×W×D) (mm)	Weight (kg)	Conveying Pipe Dia. (inch)	(inch)	
SHR-3U	3	380×250×330	4	1.5	1.5	
SHR-6U	6	420×285×360	6	1.5	1.5	
SHR-12U	12	470×315×400	7	1.5	1.5	
SHR-24U	24	690×315×400	9	2	2	
SHR-36U	36	930×315×400	11	2	2.5	
SHR-48U	48	975 × 350 × 485	15	2.5	3	
SHR-96U	96	1220×430×560	20	2.5	3	



SHR-U-S

SHR-U-S(ES)-(T) Series

■ Coding Principle





Features

- This series of centralized hopper receiver can work with the most of central vacuum units such as SAL-UG 122/124 and central conveying system.
- SHR-U-S receiver is suitable for mounting on the dryer, storage tank, or machine hopper.
- SHR-U-E receiver is designed to be mounted directly on feeding throat of the plastic processing machine. It required no machine hopper and kept very little dried material before the process.
- SHR-U-S-T or SHR-U-ES-T can work with multi-component batch blending or injection application. The three-way vacuum pipe allows easy connection of vacuum pipe from receiver to reciever in short proximity application.
- Stainless steel hopper receiver
- The vacuum valve is used to ensure a good vacuum line without compromising the most demanding conveying capacity.
- Standard equipped with steel wired mesh filter screen.

SHR-U-ES




SHR-U-ST

SHR-U-S/ES-(T) Series

Accessory & Options


- Multiple-functuional installation frame HMB suitable for other mounting application with max. 900mm adjustable diameter. Add "A" at the end of the model code.
- SHR-U-S can work with storage collective hopper SCH-U/SICH-U in the direct feeding throat mounting application.
- The optional material one-way flap on each receiver to ensure good vacuum in the common material line conveying system. Add "RSV" at the end of the model code.
- The optional pneumatic material shut-off valve on each receiver to ensure ideal vacuum in the common material line conveying system. Add "PSV" at the end of the model code.
- The material discharge flap with extra thickness. Add "SD" at the end of the model code.
- Anti-bridge option at the material outlet for SHR-48U. Applicable for flowing material but bridging from time to time only. Add "MB" at the end of the model code.


 The optional pneumatic check valve is available for SHR-12U/24U/36U-S to avoid suck-back when the material pipe is shared by several hoppers, and add "PSV" at the end




Multifunctional installation frame

Base Flange







SHR-3U-S SHR-48U-S~SHR-96U-S SHR-6U-S~SHR-36U-S


SHR-U-S Specifications


	Receiver			Convieying	Vacuum
Model	Capacity (L)	Dimension (H×W×D) (mm)	Weight (kg)	Pipe Dia. (inch)	Pipe Dia. (inch)
SHR-3U-S	- 3	600×270×340	4.5	1.5	2
SHR-3U-ES		745 × 270× 330	4.5	1.5	2
SHR-6U-S	- 6	560 × 305 × 375	7.5	1.5	2
SHR-6U-ES	3	730 × 305 × 375	9.5	1.5	
SHR-12U-S	12	615×335×405	9	1.5	2
SHR-12U-ES	12	810 × 335 × 405	14	1.5	
SHR-24U-S	- 24	825×335×405	11	2	2.5
SHR-24U-ES	24	1255× 400 × 405	15	2	2.5
SHR-36U-S	36	1035 × 335 × 405	12	2	2.5
SHR-48U-S	48	1140×400×480 18		2.5	3
SHR-96U-S	96	1400 × 480 × 560	23	2.5	3

SHR-U-S Base mounting dimensions

Model	L(mm)	L1(mm)	d(mm)	R(mm)
SHR-3U-ES	120	50	40	6.5
SHR-6U-ES	150	70	55	6.5
SHR-12U-ES	180	80	55	6.5
SHR-24U-ES	180	85	80	6.5







3110-0-31	Specifications	

	Hopper			Convieying	Air Suction
Model	Hopper capacity (L)	Dimension (H×W×D) (mm)	Weight (kg)	Pipe Dia. (inch)	Pipe Dia. (inch)
SHR-3U-ST	3	600×260×370	4.5	1.5	2
SHR-3U-EST	3	745 × 235× 370	4.5	1.5	۷
SHR-6U-ST	6	560 × 290 × 400	7.5	1.5	2
SHR-6U-EST	U	727 × 280 × 400	9.5	1.5	
SHR-12U-ST	12	615×305×440	9	1.5	2
SHR-12U-EST	12	810×305×440	14	1.5	2
SHR-24U-ST	24	825 × 305 × 455	11	2	2.5
SHR-24UEST	24	1255× 400 × 455	15	۷	2.5
SHR-36U-ST	36	1035×305×455	12	2	2.5
SHR-48U-ST	48	1145×350×515	18	2.5	3
SHR-96U-ST	96	1400 × 430 × 560	23	2.5	3


SHR-U-EST Base mounting dimensions

Model	L(mm)	L1(mm)	d(mm)	R(mm)
SHR-3U-EST	120	50	40	6.5
SHR-6U-EST	150	70	55	6.5
SHR-12U-EST	180	80	55	6.5
SHR-24U-EST	180	85	80	6.5



SHR-P-U Series

■ Coding Principle



Features


- This series of power receiver can work with the main vacuum units such as SAL-UGP.
- SHR-P-U consists of two categories, the cloth mesh filter and the plate filter.
 Cloth mesh filter is used to convey materials with powder content ≤30%, plate filter is used to convey materials with powder content >30%.
- Stainless steel hopper receiver.
- The vacuum valve is used to ensure a good vacuum line without compromising the most demanding conveying capacity.
- All models equipped with auto-purge after each conveying cycle. It maintains a good conveying result and reduces maintenance.

Accessory & Options

• Collective hopper SCH-P-30U/60U/90U is available for SHR-P-30U/60U/90U.





Storage Collective Hopper(Optional)



Base Flange

Outline Drawings






■ Specifications

•								
Model	SHR-P-12U	SHR-P-30U	SHR-P-30U-1	SHR-P-30U-2	SHR-P-60U	SHR-P-60U-3	SHR-P-90U	SHR-P-90U-5
Hopper capacity (L)	12	30	30	30	60	60	90	90
H(mm)	940	1325	1325	1325	1500	1500	1640	1640
W(mm)	535	730	730	730	780	780	890	890
D(mm)	380	470	470	470	500	500	635	635
d3(mm)	Ф197	Ф430	Ф430	Ф430	Ф490	Ф490	Ф600	Ф600
d1(mm)	Ф231.5	Ф413	Ф413	Ф413	Φ475	Ф475	Ф583	Ф583
d2(mm)	Ф254.6	Ф383	Ф383	Ф383	Ф440	Ф437	Φ550	Ф550
d5(mm)	Ф271	_	-	-	-	-	_	-
d4(mm)	Ф9	Φ7	Ф7	Φ7	Ф7	Ф7	Ф9	Ф9
d6(mm)	Ф4	-	-	-	-	-	-	-
d7(mm)	-	Ф100	Ф100	Ф100	Ф127	Ф127	Ф152.4	Ф152.4
d8(mm)	- ,	Ф11	Ф11	Ф11	Ф11	Ф11	Ф11	Ф11
h(mm)	-	428	428	428	516	516	637	637
L1(mm)	-	180	180	180	180	180	180	180
L2(mm)	_	210	210	210	210	210	210	210
Weight(kg)	27	57	60	63	60	69	72	87
Conveying Pipe Dia. (inch)	1.5	1.5	1.5	1.5	2.0	2.0	2.5	2.5
Vacuum Pipe Dia. (inch)	1.5	1.5	1.5	1.5	2.0	2.0	2.5	2.5



SHR-P-U/SCH(-U)/SICH-U Series

■ Coding Principle




Features

- Mainly work with Compact Dryer SCD-OP
- It can remove the powder in the material to avoid stains generating in the molding process.
- Adopts stainless steel SUS304 to ensure no material contamination
- Standard equipped wtih adjustable level sensor

Specifications

Норрег							Air Suction
Model	Hopper capacity (L)	Dust-removing efficienvy	Handling capacity (kg/hr)	Dimension (H×W×D) (mm)	Weight (kg)	Conveying Pipe Dia. (inch)	Pipe Dia. (inch)
SHR-CP-3U	3	80%	10	820 × 280× 305	8	1.5	1.5

Outline Drawings






Base Flange

SCH(-U)/SICH-U Series


Coding Principle




■ Features

- SCH-U and SICH-U are mainly to work with the SHR-U vacuum hopper receiver and SHR-U-S U series central vacuum hopper receiver
- Heat-insulated collective hopper SICH-U ensures temperature decrease no more than 30°C within 30 minutes
- SCH-U and SICH-U are made of stainless steel, which ensure no material contamination

Outline Drawings





Specifications

SICH-U

Model	Hopper capacity (L)	Dimension (H×W×D) (mm)	Weight (kg)
SICH-6U	6	340 × 345× 300	8
SICH-12U	12	425 × 405× 350	11
SICH-24U	24	535 × 490× 430	15

SICH-U Base Flange

Model	L(mm)	L1(mm)	d(mm)	R(mm)
SICH-6U	150	81	51.5	6.5
SICH-12U	150	81	55	6.5
SICH-24U	180	85	64.5	6.5

SCH-U

Model Hopper capacity		Dimension (H×W×D) (mm)	Weight (kg)
SCH-6U	6	257×300×317	4.5
SCH-12U	12	314×362×381	7
SCH-24U	24	329 × 404× 423	9
SCH-36U	36	448 × 404× 423	11

SCH-U Base Flange

Model	L(mm)	L1(mm)	d(mm)	R(mm)
SCH-6U	150	80	58.5	6.5
SCH-12U	150	80	58.5	6.5
SCH-24U	180	85	81.5	7
SCH-36U	180	85	81.5	7